Actuators can be delivered with external Oden remote box for manual use. You select first in OVP-V.23A program what happens with actuator if control, signal looses. If selecedt: actuator goes to 3-point control mode, When 4-20mA control signal is switched off by turning the key to the MAN mode in Oden remote box, actuator can be controlled by this external Oden remote control box.

In this Oden remote box there is 2 push buttons to increase or decrease control signal to actuator.

You get even feedback signal from actuator about the actual actuator position. That can be shown in display in % (0-100%) Oden remote box have own 24 V DC power supply for 3- point control.

When you turn the key to AUT mode ( 4-20mA control signal,) actuator will go automatically to remote mode!

Ask for more information from your Oden actuator supplier or Oden Control AB